

OSA20

Optical Spectrum Analyzer

Spectral Range:
1250–1700 nm

Resolution Bandwidth:
20 pm

Key Features

Fast & Accurate

- Sweep speed: 2000 nm/s
- Wavelength accuracy: ± 10 pm
- Built-in calibration source

Easy to Use


- Intuitive user interface
- 12 inch touch-screen

Modern Interfaces

- Remote operation: Ethernet, GPIB, USB-B
- External screen: HDMI, DVI, VGA
- External devices: USB 2.0-A, USB 3.0-A

Efficient Analysis

- 8 application-oriented analysis modes
- Full suite of analysis tools




Gas Cell Analysis

Yenista's OSA20 is the most practical, high performance Optical Spectrum Analyzer on the market today. It is the fastest diffraction-grating based instrument operating from 1250 to 1700 nm. Designed around **Yenista's** renowned filter technology, the OSA20 provides a fast, accurate, high dynamic range scan, eliminating compromises of conventional instruments. It is also the first instrument of its type to incorporate a touch sensitive display with multi-touch gesture control.

Fast

The OSA20 is the fastest OSA of its kind with a maximum sweep speed of 2000 nm/s. It uses a fixed monochromator bandwidth of 20 pm and a fixed sampling resolution of 2 pm for all scans. This means every measurement is taken at the highest resolution and the highest accuracy. Sweep speed is determined solely by the choice of the sensitivity level.



The sweep speed defines the sweep time over a user defined span whereas the sweep rate defines the complete sweep cycle over this span. Typical sweep data for a sensitivity level of -60 dBm at center wavelength of 1475 nm (without analysis) is provided below.

Sweep / Span @ -60 dBm	Sweep Time	Sweep Rate	# Points
Sweep cycle / 1 nm	1.6 ms	110 ms	501
Sweep cycle / 10 nm	14.2 ms	142 ms	5001
Sweep cycle / 100 nm	131 ms	300 ms	50,001
Sweep cycle / 450 nm	640 ms	890 ms	225,001

The **Burst** sensitivity is adapted to burst signals and dedicated to GPON measurements. The duty cycle must be in the range 2–100 % with a period between 124 and 2001 μ s.

Easy to Use

Multi-touch Gesture Control

The OSA20 is operated through its 12 inch capacitive touch screen with multi-touch gesture control, an industry first. This allows very fast navigation, scrolling and zooming in an intuitive manner.

Keyboard and mouse control are also available through the USB interfaces.

Accurate

Wavelength

The opto-mechanic design of the OSA20 guarantees excellent wavelength repeatability and uniform performance over the full wavelength range from 1250 to 1700 nm. Combined with an internal acetylene gas cell, this provides unparalleled wavelength accuracy.

- **Absolute wavelength accuracy:**
 - ± 10 pm over 1500–1640 nm
 - ± 25 pm over 1250–1700 nm
- **Wavelength repeatability: ± 2 pm**

Monochromator

Yenista's renowned filter technology is used to create a monochromator with extremely sharp edges and an extremely low level of stray-light. These are key parameters to obtain highly resolved measurements in combination with a high dynamic range. The dynamic range in the vicinity of the filter curve is commonly called optical rejection ratio (ORR).

- **ORR ≥ 55 dB beyond ± 0.1 nm from the peak**
- **Stray light suppression ratio ≥ 73 dB**


In addition to the native bandwidth of 20 pm, the spectral resolution bandwidth is adjustable. You can select the desired spectral resolution bandwidth:

- **from 50 to 2000 pm with a 1 pm step** on the abscissa in nm
- **from 6 to 400 GHz with a 0.1 GHz step** on the abscissa in THz

Optical Power

The monochromator optics is achromatic, enabling accurate power measurements over the full wavelength range.

- **Level/Wavelength Flatness:**
 - ± 0.15 dB over 1500–1640 nm
 - ± 0.25 dB over 1250–1700 nm



Efficient Analysis

Built-in Analysis Modes


The OSA20 integrates one general operation mode and various built-in application-oriented analysis modes. Each mode has a full suite of analysis tools.

OSA – Optical Spectrum Analyzer (general)

General operation mode containing most of the analysis tools available on the OSA20.

WDM – Wavelength Division Multiplexing

This mode is for transmission system analysis: characterization of WDM signals such as Coarse WDM, Dense WDM and ROADM.



WDM Analysis Mode Window

MML – Multimode Laser

Characterization of multi-mode laser sources such as Fabry-Perot laser diodes.

RLT – Recirculating Loop Transmission

This mode is a special version of WDM that takes into account long distance transmission system analysis with a recirculating loop.

OFA – Optical Fiber Amplifier

Characterization of Optical Fiber Amplifiers such as Erbium Doped Fiber Amplifier.

SML – Single Mode Laser

Characterization of single mode lasers such as distributed feedback Bragg laser diodes and external cavity lasers.


BBS – Broadband Source

Characterization of Broad Band Sources such as Semiconductor, Raman or Fiber Optical Amplifiers and superluminescent or Edge-Emitting LED.

PCT – Passive Component Tester

Characterization of passive components such as optical filters, isolators or fibers.

Rack Mount Kit



Rack mount kit

Yenista has designed a special rack mount that enables integrating the OSA20 into a test system for manufacturing. It is a self-supporting assembly of 19 inch width and 8U height.

The kit can be ordered in addition to the OSA20.

Functions


Scan Measurement	<ul style="list-style-type: none"> • Auto set, Single, Continuous • Manual or Triggered scan • Sensitivity from -75dBm to -55 dBm, with an additional sensitivity level dedicated to Burst signals • Adjustable resolution bandwidth
Traces	<ul style="list-style-type: none"> • 8 traces • Traces types: Store, Live, Average, Rolling Average, Hold Min/Max, Calculate (+ and - lin and - log) • Commands: save, load, copy, paste, display/hide
Analysis parameters	Auto analysis, noise level, analysis on a selected area of the graph
Analysis tools	Peak Trough Search, Spectral Width, xdB Width, λ_{mean} , λ_{peak} , λ_{center} and σ , FWHM, Side Modes Spacing, notch Width, SMSR, OSNR, Ripple, Optical Power, Peak Power Density, Channel Detection, Loss Measurements, Pass Band Test, Stop Band Test
Graph display	<ul style="list-style-type: none"> • 4 markers • Multiple zoom commands and graphical display items
Data Handling	<ul style="list-style-type: none"> • Saving/loading: settings, analysis results, screenshots • Commands: save, load, copy, paste • 2 GB storage on internal drive
Other	Auto-calibration, remote control

Modern Interface

The connectors are located on the right panel of the instrument for easy access.

- To connect devices such as keyboard and mouse, a USB key or disk to export your measurement results, or an external multi-touch screen: 2 USB 3.0-A ports and 4 USB 2.0-A ports (2 on the front panel)
- To remotely control the instrument: 1 USB 2.0-B port, 1 GPIB port and 2 Ethernet ports
- To connect an external screen: you can choose from HDMI, DVI or VGA
- To synchronize scans with a signal: Trigger In and Out connectors

Connector Cleaning



Optical Connectors

To maintain the lowest losses and easy maintenance, optical connectors are mounted on a plate that you can unscrew to clean them easily, as shown in the illustration.

Specifications

Wavelength	Spectral Range	1250–1700 nm	
	Span Range	0.5 nm to full range (450 nm)	
	Linearity*1	±6 pm over 1500–1640 nm, ±20 pm over full range	
	Accuracy*1	±10 pm over 1500–1640 nm, ±25 pm over full range	
	Repeatability	±2 pm	
	Sampling Resolution	2 pm	
	Sampling Points	251 (span of 0.5 nm) to 225,001 (span of 450 nm)	
	Reference	Built-in ELED (safety class 1) + Acetylene cell (user calibration by patch cord)	
Monochromator	Resolution Bandwidth*2*3*4	20 pm native, adjustable over 50–2000 pm with 1 pm step	
	Dynamic Range (ORR)*5	≥ 30 dB (> 35 dB typ.) beyond ±50 pm from peak ≥ 50 dB (> 55 dB typ.) beyond ±100 pm from peak ≥ 60 dB (> 63 dB typ.) beyond ±200 pm from peak	
	Stray Light Suppression Ratio*6	≥ 73 dB	
Optical Power	Input Power per Channel	≤ 20 dBm	
	Total Safe Power	≤ 25 dBm	
	Level Sensitivity*7	single scan	High (0.5 nm/s): < -76 dBm (-78 dBm typ.)
		with averaging (Avg Nb of scans)*8	High (0.5 nm/s): -80 dBm (Avg 3), -85 dBm (Avg 30), -90 dBm (Avg 380) -75 dBm (2 nm/s): -80 dBm (Avg 7), -85 dBm (Avg 70), -90 dBm (Avg 800)
	Absolute Level Accuracy*1*9	±0.4 dB at 1310 nm and 1550 nm	
	Level Linearity*10	±0.07 dB over the full range (input level -50 to +3 dBm)	
	Level/Wavelength Flatness*11	±0.15 dB over 1500–1640 nm, ±0.25 dB over 1260–1680 nm	
Level Sampling	±0.01 dB over -60 to +20 dBm		
Sweep Speed	Sensitivity*7	-55 dBm at 2000 nm/s to -75 dBm at 2 nm/s	
	Sweep Cycle/100 nm*12	300 ms typ.	
	Sampling Rate	1 MHz typ.	
Optical Interfaces	Optical Input	SMF-28 type fiber	
	Calibration Output	Wavelength reference (see above)	
	Connector of Input and Output	FC/APC or FC/PC or SC/APC or SC/PC	
	Return Loss	> 38 dB (> 42 dB typ.) at 1310 nm and at 1550 nm (APC connector)	
Environmental	Operating Temperature	+5 °C to +35 °C, +41 °F to +95 °F	
	Performance Guaranteed Temp	+18 °C to +28 °C, +64.4 °F to +82.4 °F	
	Storage Temperature	-10 °C to +50 °C, +14 °F to +122 °F	
	Humidity	80 % RH, non condensing	
Physical & Electrical	Dimensions & Weight	W 413 x H 314 x D 385 mm, 15 kg	
	Power Supply	48 V DC input, ≤ 75 VA (adapter 100–240 V AC, 50–60 Hz to 48 V DC provided)	
Display	Screen	12 inch capacitive touch-screen (res. 1024 x 768)	
External Devices	Screen	VGA Port (x1), DVI-D Port (x1), HDMI (x1)	
	Others (mouse, hard disk, ...)	USB 2.0-A (x4), USB 3.0-A (x2)	
Remote Interfaces	Ethernet (2x RJ45)	1 Gb/s max.	
	GPiB (1x IEEE 488)	7.2 Mb/s max.	
	USB (1x USB 2.0-B)	115 kb/s max.	
Triggers	In	Start scan (BNC, 5 V TTL), Gate in RLT mode	
	Out	Pulse on a user-defined span (BNC, 5 V TTL)	
Data Storage	Internal	2 GB	
	External	FAT32, NTFS	
	File Types	csv, binary, jpeg, png	

*1: After user calibration performed after 1 hour warm-up time.

*2: Native 17–22 pm over 1500–1620 nm (except in -55 dBm sensitivity), 17–24 pm over 1250–1700 nm.

*3: Adjustable resolution bandwidth is calculated from the native bandwidth.

*4: Adjustable over 6–400 GHz with 0.1 GHz step on the abscissa in THz.

*5: HeNe laser at 1523 nm with ±2 nm span.

*6: Laser at 1523 nm with ±50 nm span, excluding ±2 nm around peak.

*7: Noise level of 99 % of all data points over 1520–1620 nm.

*8: Typical values.

*9: Over 18–28°C all sensitivity settings except ±0.6 dB in -55 dBm and Burst sensitivities.

*10: Measured @ 1310 nm & 1500 nm, except ±0.3 dB in -55 dBm and Burst sensitivities.

*11: Except ±0.35 dB in -55 dBm and Burst sensitivities, except for water absorption lines, over 18–28°C all sensitivity settings.

*12: Sweep cycle /100 nm at -60 dBm sensitivity at center wavelength of 1475 nm.



Contacts

Americas	sales-am@yenista.com	+1 805 367 4075
EMEA	sales-emea@yenista.com	+33 2 9648 3716
China	sales-china@yenista.com	+86 21 3251 7155
Asia Pacific	sales-apac@yenista.com	